


Position	1	2	3	4	4.1	5	6	7	8	8.1	9	10	10.1	10.2	11	12
Type	A4	A4	A4	A4		A4	A4	A4	A4		PP-A4	PP-A4			PP-A4	PP-A4
Pump (Qt.-kW)		1x4		2x0,75		1x4	1x4	2x0,75	1x2,2		1x2,2	3x0,75			2x2,6	
Filter		1x20"		2x10"		1x10"		2x10"	1x10"		1x10"	3x10"			2x air fil.	
Rinsing water consumption (L/H)				60-600				60-600				60-600				
Sump Volume (L)		235		51-54		380		51-54	255			48-51-54				
Effective contact length (mm)	500	605		2x275		1100		2x275	715			3x275				660
Ultrasound (kHz-W)		40 - 800														
D.I. water consumption (L/H)																
Module Code	1402-6	1742-6	1801-6	1707-6	1801-6	1747-6	1801-6	1707-6	1667-6		1608-6	1810-6	1403-6			
Module	Input Conveyor	Sweller Module	Squ. roll	Water Rinse	Squ. roll	Desmearing Module	Squ. roll	Water Rinse	Neutralizer Module		Water Rinse	Blow off	Exit Conveyor			



SCHEMATIC CROSS SECTION - TOP VIEW	
Desmear Line 650	
DRAWING NUMBER	SCALE
	1:30
CLIENT	DATE
	03-02-22